

# MAXIMUM PRODUCTIVITY MAXIMUM SAVINGS

**\$3,800\*** IN TOTAL SAVINGS!  
UP TO

BUY 6 MOTOROLA TWO-WAY ANALOG BUSINESS RADIOS & GET A FREE RADIO\*\*



**CLP SERIES**  
**\$369**  
VALUE



**CLS SERIES**  
**\$209**  
VALUE



**RD SERIES**  
**\$380**  
VALUE



**RM SERIES**  
**\$310**  
VALUE

Act now by visiting: [www.MyRadioReward.com](http://www.MyRadioReward.com)

AVAILABLE THROUGH

**GRAINGER**  
FOR THE ONES WHO GET IT DONE

**CLS Series:**  
CLS1110 – 22NL44  
CLS1410 – 22NL45

**CLP Series:**  
CLP1010 – 15X820  
CLP1040 – 15X821  
CLP1060 (Bluetooth) – 45L124

**RD Series:**  
RDU4100 – 23Y699  
RDU4160d – 23Y701  
RDV5100 – 23Y698

**RM Series:**  
RMU2040 – 29WJ53  
RMU2080 – 29WJ54  
RMU2080d – 29WJ55  
RMV2080 – 29WJ56  
RMM2050 – 29WJ57

For additional information about Motorola products available through Grainger, please contact your Grainger Account Representative or visit [www.grainger.com/motorola](http://www.grainger.com/motorola)

\*BASED ON THE TOTAL VALUE OF THE MAXIMUM PURCHASE OF 60 RD SERIES RADIOS. \*\*UP TO MAXIMUM LIMIT. OFFER VALID SEPTEMBER 1 THROUGH DECEMBER 31, 2016.

# MAXIMUM PRODUCTIVITY MAXIMUM SAVINGS

UP TO **\$3,800\*** IN TOTAL SAVINGS! BUY 6 MOTOROLA TWO-WAY ANALOG BUSINESS RADIOS AND GET A FREE RADIO\*\*

**CLP Series:** CLP1010 – 15X820, CLP1040 – 15X821, CLP1060 (Bluetooth) – 45L124; **CLS Series:** CLS1110 – 22NL44, CLS1410 – 22NL45; **RM Series:** RMU2040 – 29WJ53, RMU2080 – 29WJ54, RMU2080d – 29WJ55, RMV2080 – 29WJ56, RMM2050 – 29WJ57; **RD Series:** RDU4100 – 23Y699, RDU4160d – 23Y701, RDV5100 – 23Y698

Enabling your workforce with the right communication tools empowers them to accomplish more, and can make all the difference to your bottom line. Simply put, Motorola two-way radios are the answer to everything from clearer communication and easier usage, to the uninterrupted performance on the job†. Find ergonomic design, crisp audio quality and long-lasting battery life in all of Motorola's business models. Additionally, all of our radios are narrowband compliant.

†COVERAGE MAY VARY BASED ON TERRAIN AND CONDITIONS

**CLP SERIES RADIOS:** The CLP's small, unobtrusive design packs a big punch in a lightweight, palm-sized package and offers the most reliable communications in even the noisiest of environments. The CLP 1060/63 six-channel radios are Bluetooth™ capable. The CLP single- and four-channel models feature wired headphones. All CLP radios bring a choice of 90 UHF business-exclusive frequencies. They are easily operable and come standard with push-to-talk functionality and an extended battery life. These radios meet military standards for shock, vibration, temperature and antimicrobial protection.

**CLS SERIES RADIOS:** Rely on impressive coverage capability in this compact radio. It operates on 56 business-exclusive frequencies and includes a coverage range of up to 200,000 square feet, or the equivalent of 15 floors, with the choice of either single- or four-channel models. Intuitive and user friendly, the CLS' streamlined design is fronted by a crystal-clear LCD display. The CLS (Clear, Light, Simple) Series meets military standards for shock, vibration, temperature and antimicrobial protection.

**RD SERIES RADIOS:** Introduce your workers to the perfect business partner that will make any workplace environment more productive for them and more profitable for you. Not even the harshest job-site conditions stop the affordable, easy to use RD on-site business radio. Enhanced wattage extends coverage to up to 30 floors/350,000 square feet (4/5 Watt radio models). Its outstanding industrial design features a heavy-duty metal body that meets military standards for shock, vibration, water, dust and temperature, and protects its premium performance: exceptional audio quality, easy programming of frequencies and radio settings, advanced voice activation, flexible battery life solutions, and easy cloning.

**RM SERIES RADIOS:** Empowering your workforce with a reliable, long-lasting audio solution is the hallmark of the RM Series. Capable of customizing channels per radio via voice alias, the RM has a coverage range of up to 250,000 square feet (20 floors) and can operate on either four or eight channels, across each UHF, VHF and MURS frequency. Count on up to 12-hour battery life without the Battery Save feature and up to 15-hour battery life with the Battery Save feature. The RM Series radios meet military standards for shock, vibration, water, dust, temperature and antimicrobial protection.

\*BASED ON THE TOTAL VALUE OF THE MAXIMUM PURCHASE OF 60 RD SERIES RADIOS.

\*\*UP TO MAXIMUM LIMIT.

## PROMOTION TERMS & CONDITIONS:

1. Promotion valid only on qualifying Motorola Solutions ("Motorola") CLS, CLP, RD, and RM Series two-way radios ("Eligible Radios") purchased from a Motorola Authorized Business Radio Reseller between September 1, 2016 – December 31, 2016 ("Promotion Period"). Promotion excludes CLS1000, CLS1450c and all bulk (non-packaged) purchase models.
2. End-User Customer ("End-User") receives 1 free radio after each purchase of 6 CLS Series Radios (CLS1110, CLS1410) or 6 CLP Series Radios (CLP1010, CLP1040, CLP1060) or 6 RD Series Radios (RDU4100, RDV5100, RDU4160d) or 6 RM Series Radios (RMU2040, RMU2080, RMU2080d, RMM2050, RMV2080). End-User can purchase as many eligible radios as needed, but the free radio offer will be limited to a maximum of 10 total redemptions (or 60 radio units purchased) per customer/company.
3. Value for the free radio on each qualifying purchase of 6 CLS Series Radios is \$209US, 6 CLP Series Radios is \$369US, 6 RD Series Radios is \$380US, 6 RM Series Radios is \$310US (up to maximum qualifying limit).
4. No cash will be provided. No extended delivery dates are allowed under these offers. All transactions are subject to validation.
5. Promotions good only in the U.S and Puerto Rico and is void where prohibited, taxed or restricted by law.
6. To receive the product after each purchase of six (6) qualifying CLS, CLP, RD, or RM Series Radios (limited to a maximum of 10 total redemptions), End-User must completely fill out the online submission form available at [www.myradioreward.com](http://www.myradioreward.com) and supply all requested documentation. All claims must be entered by 11:50pm EST on Friday, January 13, 2017.
7. Products cannot be mailed to a PO Box. For promotion questions, please call 1-800-699-2512 or email [myradioreward@360incentives.com](mailto:myradioreward@360incentives.com). Please allow 4-6 weeks from receipt of your submission to receive your product(s).
8. This promotion may not be combined with any other promotional offers, rebates, coupons or discounts. This promotion is not transferable. Any requests that do not comply with the terms of this promotion will be rejected. This promotion is subject to all local laws and regulations.
9. Motorola is not responsible for lost, late, mutilated, misdirected or postage due mail and shall not be responsible for any shipping or invoice delays. Motorola and its agents have the right to audit, validate or verify any purchases claimed and serial numbers submitted. Eligible Radios purchased and subsequently returned for refund are not eligible for the promotion. Duplicate requests will not be considered.
10. Fraudulent submissions could result in prosecution. The submission of false, incorrect, misleading or fraudulent information or documentation may result in disqualification from this promotion and from future Motorola promotions.
11. Motorola reserves the right to modify, withdraw or cancel this promotion at any time, with or without any prior notice. Please make a copy of all materials submitted.
12. This offer is subject to product availability.



Motorola Solutions, Inc. 1301 East Algonquin Road, Schaumburg, Illinois 60196, U.S.A. 800-367-2346 [motorolasolutions.com](http://motorolasolutions.com)

MOTOROLA, MOTO, MOTOROLA SOLUTIONS and the Stylized M Logo are trademarks or registered trademarks of Motorola Trademark Holdings, LLC and are used under license. All other trademarks are the property of their respective owners. © 2016 Motorola Solutions, Inc. All rights reserved.